## STEALTH® Pharmaceutical Metal Detector



Pharmaceutical metal Stealth detectors are manufactured to suit Pharmaceutical and/or Nutraceutical applications. Stealth detectors use digital signal processing technology and have high sensitivity levels to ensure the detection of the smallest ferrous, non-ferrous and stainless steel contaminants. The built-in data collection software with USB connectivity establishes the Stealth as an effective critical control point complying with stringent HACCP regulations.

### THE FORTRESS ADVANTAGE:

- "Never Obsolete" Commitment: detectors are always supported with parts and services
- Standard electronics configuration across product line allowing easy support and trouble shooting
- Modular design; have fewer components
- Custom built detectors or stock sizes
- Simple Operation, Outstanding Reliability, **Exceptional Performance**

## **KEY FEATURES:**

- Contact Reporter Software Included
- Digital Signal Processing Technology
- Ultra Sensitive Detection
- AutoTest: Self Diagnostic Testing
- Easy "Fast" Calibration
- Automatic Configuration for Iron-Enriched
- System Set-Up in Seconds
- Flash Memory Stability
- Multi-Level Password Protection
- Detailed USB Data Collection
- FDA Compliant
- Compatible with High Speed lines
- Adjustable Height and Tilt
- Validation Package Included

### **APPLICATIONS:**

- Tablets
- Pharmaceuticals
- Capsules
- Bubble Gum Tablets
- Nutraceuticals
- Extruded Candy

Don't See Your Application? Please Contact Us!

### **AVAILABLE OPTIONS:**

Contact Communication Software




Fortress Technology Inc. 51 Grand Marshall Dr. Toronto, ON, M1B 5N6 Canada Tel: 1-888-220-8737

Fortress Technology (Europe) Ltd. The Phantom Building 7 Beaumont Road, Banbury, OX16 1RH UK Tel: +44 (0) 1295 256 266 sales@fortresstechnology.com sales-UK@fortresstechnology.com vendas@fortress-iis.com.br

Fortress Technology Sistemas de Inspeção Ltda. ROD. Presidente Tancredo de Almeida Neves 3007 - Km 30,5 - Vila Rosina Caieiras - São Paulo, CEP: 07748-400 Fone: 55-11-3641-6153



# STEALTH® Pharmaceutical Metal Detector



## **DETECTOR OPTIONS & SPECIFICATIONS:**

Sensitivity	0.15mm Ferrous and Non-Ferrous, 0.3mm Stainless Steel (300 series)
Throughput	Up to 30,000 tablets per minute
Construction	316 Stainless Steel
 Extra-Rugged Casing	Vibration immunity and stability in heavy duty applications and harsh environments
 Rating	Nema 4X / IP69K
 Network Communications	RS485, Ethernet / Wireless via Contact Communications Software
 Electrical	100-240v Single phase, 1amp, 50-60Hz

